



TF Card



Air filter
× 5



User manual



Full Face Mask



Air tubing



T-junction



Power supply



Travel bag


Auto BIPAP VM-7&VM-8

American Sensor


Intelligent Breathing Algorithm

Improve Overall Breathing

German Technology



Patient-device synchrony
Real-time displaying



Whisper quiet
light and compact



Efficient heating
humidifier system



Professional sleep study report

Unique sleep study report of whole week & month.

New operating system is easier to operate, interface is more exquisite.



Specification

Description	Auto BIPAP VM-7	Auto BIPAP VM-8
Work Mode	CPAP, Auto,S, T, ST, Auto S	CPAP, Auto,S, T, ST, Auto S, APCV
Sound	<28 dB	
Screen	2.8 inch TFT, 320 x 240	
Pressure Range	4-25 cmH2O	4-30 cmH2O
IPAP	4-25 cmH2O	4-30 cmH2O
EPAP	4-20 cmH2O	4-20 cmH2O
Data Storage	TF Card	
Power Supply	Input 100-240V, 50-60Hz, 1-2A; Output + 24V, 2.5A	
DC Voltage	24VDC, 2.5A	
Over-Temperature Protection	Stop automatically, alarm with 4 times	
Lock Function	Yes	
Screen Auto Sleep	Auto sleep in 15 minutes, press any button to highlight screen	
Backup Rate	5-50min, adjustable	
I/E	10-80%	
Ramp Item	0-60min adjustable 1min/Step	
Auto ON/Off	Yes	
Inspirate Triggler	1-5 level	
Expirate Level	1-5 level	
Inspirate Sensitivity	1-5 level	
EPR	Yes, 0-3 level	
Auto-Altitude	Yes	
Leak Compensation	Yes	
Awake Detection	Yes	
Breath Event Detection	Yes	
Water Capacity	200ML max	
Humidifier Level	Integrated Heated, 0-5 level	
Alert	Power off, mask off	
Dimensions(cm)	29L x 15W x 10H(machine)	
Carton Dimensions(cm)	34.5L x 20.5W x 25.5H(1pc carton)	
	40L x 34.5W x 25.5H(2pcs carton)	
	59.5L x 34.5W x 25.5H(3pcs carton)	
Weight(with humidifier)	1.7Kg(net weight); 4.0Kg(gross weight)	
Work For	OSA,CSA,MSA,COPD	



Hunan VentMed Medical Technology Co., Ltd.

Factory: Baoqing industrial park, Shaoyang, Hunan, China

Office: +86-739-5188959 Web: www.ventmed.net